

# contacta |11.

HLD9

## HLD9

Our HLD9 is a pinoneering modular hearing loop driver for perimeter or phased array configurations, suitable for large area applications such as theatres, conference facilities, sports arenas, concert halls and auditoria.

As a Class D driver, it manages power extremely efficiently meaning that it emits very little heat from its compact packaging.

To make the experience of using it as simple as possible, the driver includes sophisticated communication capabilities enabling remote set-up and control of levels, as well as system interrogation and performance monitoring.

#### **Features**

- Built-in 90° phase shift
- Flexible configuration
- Ultra efficient power utilisation
- Sleep mode
- High frequency compensation
- Continuous self-testing
- Accurate, lockable controls (front panel mounted)
- Input and drive level indication
- Intelligent protection system
- Flexible audio inputs
- Interface to external communication devices

#### **Standards**

- FCC class "B" EMC (emissions)
- IEC 60118-4:2006 (in correct installations)
- BS EN 55103-1:2009 (EMC emissions)
- BS EN 55103-2:2009 (EMC immunity)

# **Applications**

Suitable for facilities such as:

- Theatres
- Concert halls
- Places of worship
- Sports arenas
- Conference facilities

Talk to us now: +44 (0) 1732 223900 (UK & ROW) +1 616 392 3400 (US & Canada) www.contacta.co.uk



# **Physical Data**





## **Technical Data**

Inputs	Input 1 (Microphone)	Balanced XLR with switchable phantom power or $^{1\!4''}$ TRS jack for electret microphone with 3.3VDC power via $680\Omega$ load
	Input 2 (Line)	Balanced XLR or ¼" TRS jack to ohmically isolated input
Loop output	Loop connection	4-pole speakON connector
	Loop drive current	10A RMS compliance current @ 1Khz sine wave
	Loop drive voltage	36V RMS compliance voltage
Expansion	Contacta interconnect	Input or output to or from additional Contacta products 90° phase shift selectable
Status	Volt-free relay contacts	SPCO
Feature	External monitor & control	Contacta communications processor interface
Audio	Frequency response	100 Hz – 5kHz (±3dB)
	Distortion	Better than -40dB, inputs at nominal level
Automatic Gain Control	Digitally controlled	Dynamic range: 40dB typical, Attack time: 33 milliseconds, Release time: 3.6dB per second
Controls	Microphone level	Off, then to maximum in 50 1dB increments
	Line level	Off, then to maximum in 50 1dB increments
	Loop current	Off, then to maximum in 63 1dB increments
Displays	Microphone level	8 level bar graph with peak hold, 6dB steps
	Line level	8 level bar graph with peak hold, 6dB steps
	Output drive level	8 level bar graph with peak hold, 0.6A steps
	Other indications	LEDs for all setup and status indications